

Mold Technology Ltd Po Box 34-785 Birkenhead Auckland 0746

Argofile Super Stones are made from long ceramic fibres embedded in thermoset resin, they exhibit superior strength compared to normal abrasive stones and are non clogging even under the most strenuous conditions

FLAT SUPER STONE - SELECTION CHARTA

| | r L | AI SULI | EK STO | AG - SEI | LECTIO | NUTAI | NI a | |
|-------------|---------|---------|------------|----------|--------|--------|-------------|---------|
| SIZE | EMERALD | GOLD | LIGHTBROWN | ORANGE | BROWN | BLUE | WHITE | RED |
| | (#120) | (#180) | (#300) | (#400) | (#600) | (#800) | (#1000) | (#1200) |
| 0.5x 2x100 | SE052 | SG052 | SL052 | S0052 | SP052 | SB052 | SW052 | SR052 |
| 0.5x 4x100 | SE054 | SG054 | SL054 | S0054 | SP054 | SB054 | SW054 | SR054 |
| 0.5x 6x100 | SE056 | SG056 | SL056 | S0056 | SP056 | SB056 | SW056 | SR056 |
| 0. 5x10x100 | SE051 | SG051 | SL051 | S0051 | SP051 | SB051 | SW051 | SR051 |
| 0.8x 2x100 | SE082 | SG082 | SL082 | 50082 | SP082 | SB082 | SW082 | SR082 |
| 0.8x 4x100 | SE084 | SG084 | SL084 | 50084 | SP084 | SB084 | SW084 | SR084 |
| 0.8x 6x100 | SE086 | SG086 | SL086 | S0086 | SP086 | SB086 | SW086 | SR086 |
| 0. 8x10x100 | SE081 | SG081 | SL081 | S0081 | SP081 | SB081 | SW081 | SR081 |
| 1. 0x 2x100 | SE102 | SG102 | SL102 | S0102 | SP102 | SB102 | SW102 | SR102 |
| 1. 0x 4x100 | SE104 | SG104 | SL104 | S0104 | SP104 | SB104 | SW104 | SR104 |
| 1.0x 6x100 | SE106 | SG106 | SL106 | S0106 | SP106 | SB106 | SW106 | SR106 |
| 1. 0x10x100 | SE110 | SG110 | SL110 | 50110 | SP110 | SB110 | SW110 | SR110 |
| 1.5x 2x100 | SE152 | SG152 | SL152 | S0152 | SP152 | SB152 | SW152 | SR152 |
| 1.5x 4x100 | SE154 | SG154 | SL154 | S0154 | SP154 | SB154 | SW154 | SR154 |
| 1.5x 6x100 | SE156 | SG156 | SL156 | S0156 | SP156 | SB156 | SW156 | SR156 |
| 1. 5x10x100 | SE150 | SG150 | SL150 | S0150 | SP150 | SB150 | SW150 | SR150 |
| 2. 0x 2x100 | SE202 | SG202 | SL202 | S0202 | SP202 | SB202 | SW202 | SR202 |
| 2. 0x 4x100 | SE204 | SG204 | SL204 | 50204 | SP204 | SB204 | SW204 | SR204 |
| 2. 0x 6x100 | SE206 | SG206 | SL206 | S0206 | SP206 | SB206 | SW206 | SR206 |
| 2. 0x10x100 | SE210 | SG210 | SL210 | S0210 | SP210 | SB210 | SW210 | SR210 |
| 3. 0x 2x100 | SE302 | SG302 | SL302 | 50302 | SP302 | SB302 | SW302 | SR302 |
| 3. 0x 4x100 | SE304 | SG304 | SL304 | 50304 | SP304 | SB304 | SW304 | SR304 |
| 3. 0x 6x100 | SE306 | SG306 | SL306 | 50306 | SP306 | SB306 | SW306 | SR306 |
| 3. 0x10x100 | SE310 | SG310 | SL310 | 50310 | SP310 | SB310 | SW310 | SR310 |
| 0.5x 2x150 | SE052L | SG052L | SL052L | S0052L | SP052L | SB052L | SW052L | SR052L |
| 0. 5x 4x150 | SE054L | SG054L | SL054L | S0054L | SP054L | SB054L | SW054L | SR054L |
| 0.5x 6x150 | SE056L | SG056L | SL056L | S0056L | SP056L | SB056L | SW056L | SR056L |
| 0. 5x10x150 | SE051L | SG051L | SL051L | S0051L | SP051L | SB051L | SW051L | SR051L |
| 0.8x 2x150 | SE082L | SG082L | SL082L | S0082L | SP082L | SB082L | SW082L | SR082L |
| 0. 8x 4x150 | SE084L | SG084L | SL084L | S0084L | SP084L | SB084L | SW084L | SR084L |
| 0.8x 6x150 | SE086L | SG086L | SL086L | S0086L | SP086L | SB086L | SW086L | SR086L |
| 0. 8x10x150 | SE081L | SG081L | SL081L | S0081L | SP081L | SB081L | SW081L | SR081L |
| 1. 0x 2x150 | SE102L | SG102L | SL102L | S0102L | SP102L | SB102L | SW102L | SR102L |
| 1. 0x 4x150 | SE104L | SG104L | SL104L | S0104L | SP104L | SB104L | SW104L | SR104L |
| 1. 0x 6x150 | SE106L | SG106L | SL106L | S0106L | SP106L | SB106L | SW106L | SR106L |
| 1. 0x10x150 | SE110L | SG110L | SL110L | S0110L | SP110L | SB110L | SW110L | SR110L |
| 1.5x 2x150 | SE152L | SG152L | SL152L | S0152L | SP152L | SB152L | S₩152L | SR152L |
| 1.5x 4x150 | SE154L | SG154L | SL154L | S0154L | SP154L | SB154L | SW154L | SR154L |
| 1.5x 6x150 | SE156L | SG156L | SL156L | S0156L | SP156L | SB156L | SW156L | SR156L |
| 1. 5x10x150 | SE150L | SG150L | SL150L | S0150L | SP150L | SB150L | SW150L | SR150L |
| 2. 0x 2x150 | SE202L | SG202L | SL202L | S0202L | SP202L | SB202L | SW202L | SR202L |
| 2. 0x 4x150 | SE204L | SG204L | SL204L | S0204L | SP204L | SB204L | SW204L | SR204L |
| 2. 0x 6x150 | SE206L | SG206L | SL206L | S0206L | SP206L | SB206L | SW206L | SR206L |
| 2. 0x10x150 | SE210L | SG210L | SL210L | S0210L | SP210L | SB210L | SW210L | SR210L |
| 3. 0x 2x150 | SE302L | SG302L | SL302L | S0302L | SP302L | SB302L | SW302L | SR302L |
| 3. 0x 4x150 | SE304L | SG304L | SL304L | S0304L | SP304L | SB304L | SW304L | SR304L |
| 3. 0x 6x150 | SE306L | SG306L | SL306L | S0306L | SP306L | SB306L | SW306L | SR306L |
| 3. 0x10x150 | SE310L | SG310L | SL310L | S0310L | SP310L | SB310L | SW310L | SR310L |



Mold Technology Ltd Po Box 34-785 Birkenhead Auckland 0746

Argofile Super Stones are made from long ceramic fibres embedded in thermoset resin, they exhibit superior strength compared to normal abrasive stones and are non-clogging even under the most strenuous conditions

ROUND SUPER STONE - SELECTION CHART

| | | | _ | | - | | | |
|------------|---------|--------|------------|--------|--------|--------|---------|---------|
| 5175 | EMERALD | GOLD | LIGHTBROWN | ORANGE | BROWN | BLUE | WHITE | RED |
| SIZE | (#120) | (#180) | (#300) | (#400) | (#600) | (#800) | (#1000) | (#1200) |
| φ2.35x 50 | SED23A | SGD23A | SLD23A | SOD23A | SPD23A | SBD23A | SWD23A | SRD23A |
| φ3.00x 50 | SED3A | SGD3A | SLD3A | SOD3A | SPD3A | SBD3A | SWD3A | SRD3A |
| φ3. 18x 50 | SEDIA | SGDIA | SLDIA | SODIA | SPDIA | SBDIA | SWDIA | SRDIA |
| φ2.35x100 | SED23B | SGD23B | SLD23B | SOD23B | SPD23B | SBD23B | SWD23B | SRD23B |
| φ3.00x100 | SED3B | SGD3B | SLD3B | SOD3B | SPD3B | SBD3B | SWD3B | SRD3B |
| φ3. 18x100 | SEDIB | SGDIB | SLDIB | SODIB | SPDIB | SBDIB | SWDIB | SRDIB |

SUPER STONE HOLDERS

| CAT. NO. | · |
|----------|---------------------------------|
| SSH- 2 | FOR 2mm WIDTH STONES |
| SSH- 4 | FOR 4mm WIDTH STONES |
| SSH- 6 | FOR 6mm WIDTH STONES |
| SSH-10 | FOR 10mm WIDTH STONES |
| SSH- A | SSH-4, SSH-6, SSH-10 1PCE. EACH |
| SNH-30 | FOR 3mm ROUND STONES |

Benefits of Argfofile Super Stones

- ❖ Available in thicknesses down to 0.5mm
- ❖ High Tensile strength yet can be flexed without breaking
- ❖ Fracture free polishing of detailed areas such as narrow slots and ribs
- ❖ Aggressive stock removal when combined with ultrasonic lappers
- ❖ Can be used with Diamond paste for polishing deep slots